



Figure similar

SIMATIC DP, Connection module for PROFINET interface module ET 200 PRO IM154-3 PN HF, M12 7/8" S , 2x M12 and 2x 7/8"

Input current	
from supply voltage 1L+, max.	No current input, only infeed current, max. 8 A
from load voltage 2L+ (without load), max.	No current input, only infeed current, max. 8 A
Accessories	
Function description	IM PN; 2x M12 2x 7/8" interface module, power supply from 1L+ and 2L+ max. per 8 A, internal transfer 2L+ max. 8 A, 1L+ max. 5 A
belongs to product	ET 200pro; IM154-3 PN HF
Dimensions	
Width	60 mm
Height	130 mm
Depth	51 mm
Weights	
Weight, approx.	440 g

last modified: 8/16/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6ES71944AK000AA0](#)