

product type designation

IWLAN angular adapter RSMA/RSMA male/female
R-SMA Male/Female elbow adapter.



electrical data

number of electrical connections	2
type of electrical connection	R-SMA male / R-SMA female
transmission frequency	0 ... 6 GHz
impedance	50 Ω

ambient conditions

protection class IP	IP61
---------------------	------

design, dimensions and weights

width	17 mm
height	15 mm

standards, specifications, approvals

certificate of suitability	Yes
• RoHS conformity	

further information / internet links

internet link	http://www.siemens.com/tia-selection-tool http://www.siemens.com/snst http://www.siemens.com/iwlan http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter https://sie.ag/2QdlxcP http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com
• to website: TIA Selection Tool	
• to web page: selection aid TIA Selection Tool	
• to the website: IWLAN	
• to website: Industrial communication	
• to website: Industry Mall	
• to website: Information and Download Center	
• to website: Selection guide for cables and connectors	
• to website: Image database	
• to website: CAX-Download-Manager	
• to website: Industry Online Support	

last modified:

5/20/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6GK57981CS004AA0