



Figure similar

Siemens Low Voltage Circuit Protection OEM Disconnect & Accessories. Type: OEM DISCONNECT SWITCH Std: UL V. Rating: 600V A. Rating: 60A No. Of Poles: 3P F. Rating: 60Hz Action: single throw Mounting: FLANGE MOUNTING. O. Cycles: 10000 O. Temperature: (-20F-120F) AMBIENT TEMPERATURE Environmental Conditions: INDOOR

General technical data	
fastening method	FLANGE MOUNTING
Electricity	
voltage between phase and phase rated value	600 V
Model	
product brand name	SIEMENS
product type designation	OEM DISCONNECT SWITCH
General product approval	
certificate of suitability	UL

last modified:

1/6/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

VBFS362FPV