

MODLINK MSDD SOCKET INSERT IEC

250VAC/10A acc. EN 60320-2-2/F

Art.No.: 4000-68000-0080000

Weight: 0.026

Country of origin: DE

Model designation: Fr.Modul-C14-250-10-SO

Appliance-outlet (IEC/EN 60320-2-2/F)

Spring clamp terminals: max. 2× 2.5 mm² (AWG 14)**[Link to Product](#)****Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879038225
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	30 mm

Environmental characteristics | Climatic

Storage temperature min.	-25 °C
Storage temperature max.	60 °C

Appliance-outlet	
Connection geometry	6.3 x 0.8 mm
Operating voltage AC	250 V
Operating current	10 A
Current operating ULc	15 A
Connection	plug-in connection
No. of poles	2 + PE
Protection contact present	yes

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrelektronik:](#)

[4000-68000-0080000](#)