

MODLINK MSDD DATA INSERT

1×SUB-D9 fem./male + 1×RJ45 + 1×USB-A fem./fem.

Art.No.: 4000-68000-1430000

Weight: 0.058

Country of origin: CZ

Model designation: Fr.Modul 9Bu/St+RJ45+USB (Bu/Bu) gesch.

RJ45; USB (A); SUB-D9

1× RJ45, 8-pole metal, CAT5e (female/female)

1× USB 3.0 (female/female) form A

1× SUB-D9 (female/male)

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data

| | |
|-----------------------|---------------|
| ECLASS-6.0 | 27189217 |
| ECLASS-6.1 | 27189217 |
| ECLASS-7.0 | 27189217 |
| ECLASS-8.0 | 27189217 |
| ECLASS-9.0 | 27189217 |
| ECLASS-10.1 | 27182806 |
| ECLASS-11.1 | 27182806 |
| ECLASS-12.0 | 27182806 |
| ETIM-5.0 | EC002625 |
| customs tariff number | 85366990 |
| GTIN | 4048879037549 |
| Packaging unit | 1 |

Mechanical data | Mounting data

| | |
|--------|---------|
| Height | 88 mm |
| Width | 51 mm |
| Depth | 70,4 mm |

Environmental characteristics | Climatic

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-12-16

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

| | |
|--------------------------|-------|
| Storage temperature min. | 5 °C |
| Storage temperature max. | 40 °C |

Shielding plate

| | |
|------------------------|------------------|
| Connection information | Threaded hole M4 |
| Tightening torque | 0,9 Nm |

USB

| | |
|---------------------------------------|-------------------|
| Operating voltage AC | 48 V |
| Operating voltage DC | 48 V |
| Operating voltage AC max. (UL-listed) | 30 V |
| Operating voltage DC max. (UL-listed) | 42,4 V |
| Operating current | 1,5 A |
| USB specification | 3.0 |
| Data transmission rate max. | 5000 MBit/s |
| Looking techniques | Snap-in connector |

SUB-D9

| | |
|---------------------------------------|--|
| Operating voltage AC | 48 V |
| Operating voltage DC | 48 V |
| Operating voltage AC max. (UL-listed) | 30 V |
| Operating voltage DC max. (UL-listed) | 42,4 V |
| Operating current | 3 A |
| Current operating max. (UL) | 175 mA |
| Family construction form | SUB-D9 |
| Family type Back side | SUB-D9 |
| Gender | female |
| Gender Rear | male |
| Looking techniques | Standard UNC 4-40 screw thread bolt (EN 60807) |
| No. of poles | 9 |

RJ45

| | |
|---------------------------------------|-------------------|
| Operating voltage AC max. (UL-listed) | 30 V |
| Operating voltage DC max. (UL-listed) | 42,4 V |
| Current operating max. (UL) | 175 mA |
| Family construction form | RJ45 |
| Family type Back side | RJ45 |
| Cable category min. | Cat5e |
| Looking techniques | Snap-in connector |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrelektronik:](#)

[4000-68000-1430000](#)