

Modlight50 Pro connecting modul base mounting

Input 24VDC

Art.No.: 4000-76050-1100002

Weight: 0.1

Country of origin: ID

Model designation: Modlight50 Pro BASE MOUNTING

Base for floor mount

Connection cables are in the online shop under "Connection Technology".

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27371232
ECLASS-6.1	27371232
ECLASS-7.0	27371232
ECLASS-8.0	27371232
ECLASS-9.0	27371232
ECLASS-10.1	27371232
ECLASS-11.1	27371232
ECLASS-12.0	27371232
ETIM-5.0	EC001152
ETIM-6.0	EC001152
ETIM-7.0	EC001152
customs tariff number	85319000
GTIN	4048879751551
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V

Device protection | Electrical

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-12-17

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked
Mechanical data Material data	
Color housing	black
Material housing	Plastic
Mechanical data Mounting data	
Height	180 mm
Width	50 mm
Depth	50 mm
Environmental characteristics Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	60 °C
Connection type 1	
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	9
PIN 1	LED-Modul RD
PIN 2	LED-Modul YE
PIN 3	LED-Modul GN
PIN 4	LED-Modul BU
PIN 5	LED-Modul CL
PIN 6	Buzzer
PIN 7	24 V DC (0 V)
PIN 8	Blinking
PIN 9	0 V (24 V DC)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrelektronik:](#)

[4000-76050-1100002](#)