

**Modlight50 Pro buzzer**

4 tones

Art.No.: 4000-76050-1100004

Weight: 0.04

Country of origin: ID

Model designation: Modlight50 Pro BUZZER

Buzzer modules

**[Link to Product](#)****Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27371200
ECLASS-6.1	27371237
ECLASS-7.0	27371237
ECLASS-8.0	27371237
ECLASS-9.0	27371237
ECLASS-10.1	27371237
ECLASS-11.1	27371237
ECLASS-12.0	27371237
ETIM-5.0	EC001152
customs tariff number	85318070
GTIN	4048879751568
Packaging unit	1

**Electrical data | Supply**

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V
Current consumption max.	62,5 mA

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

**Mechanical data | Material data**

Material housing	PC
------------------	----

**Mechanical data | Mounting data**

Height	52 mm
--------	-------

Width	50 mm
-------	-------

Depth	50 mm
-------	-------

**Environmental characteristics | Climatic**

Operating temperature min.	-30 °C
----------------------------	--------

Operating temperature max.	60 °C
----------------------------	-------

**Connection type 1**

Mounting method	bayonet-locking
-----------------	-----------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrelektronik:](#)

[4000-76050-1100004](#)