

Switches Rotary Switches

6-position Vertical Type SRRN Series

Part number **SRRN151800**

⚠ Not Recommended for New Designs ⓘ



 Reference Drawings

 Inquiry

 Print

Number of wafer		1
Poles		2
Positions		5
Changeover angle		30±3°
Changeover timing		Non shorting
Actuator configuration		Round
Actuator length		20mm
Operating temperature range		-30°C to +65°C
Rating (max.)/(min.) (Resistive load)		0.15A 12V DC/50 μA 3V DC
Electrical performance	Contact resistance (Initial performance/After lifetime)	50mΩ max./100mΩ max.
	Insulation resistance	100MΩ min. 500V DC
	Voltage proof	500V AC for 1 minute
Mechanical performance	Terminal strength	5N for 1 minute
	Actuator strength	Rotational direction 1N·m
		Push direction 100N
	Wobble of actuator (load at the tip of shaft: 5N)	Measuring position from mounting surface 15mm
		Shaft wobble (max. value) 0.25mm max.
		Applicable mounting dimension 20mm
Durability	Operating life without load	10,000 cycles 70mΩ max.
	Operating life with load (at max. rated load)	10,000 cycles 100mΩ max.
Environmental performance	Cold	-40°C 96h
	Dry heat	85°C 96h
	Damp heat	40°C, 90 to 95%RH 96h
Minimum order unit(pcs.)	Japan	60
	Export	240

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alps Alpine:](#)

[SRRN151800](#)