



### Main

Accessory / Separate Part Type	Cable
--------------------------------	-------

### Complementary

Accessory / separate part designation	Bare cable
Accessory / separate part category	Cabling accessories
Cable length	328.08 ft (100 m)
Material	PvR (PVC/NBR) sheath
Color	Matt black
Cable cross section	0.00 in <sup>2</sup> (0.5 mm <sup>2</sup> )
Total number of wires	4
Wire insulation material	PVC
Flame retardance	Class C2 conforming to NF C 32-070
[Ue] rated operational voltage	300 V
[Ui] rated insulation voltage	2000 V NF C 32-201-1
Bending radius	Minimum 3 x external diameter
Tensile strength	10...35 N/mm <sup>2</sup>
Hardness	70 shores A +/-5)
Net Weight	9.90 lb(US) (4.49 kg)

### Environment

Ambient Air Temperature for Operation	-31...194 °F (-35...90 °C)
Ambient Air Temperature for Storage	-40...212 °F (-40...100 °C)
Environmental characteristic	Synthetic oils at 90 °C Mineral resistant at 90 °C Soluble resistant at 90 °C Without unmoulding agent

### Ordering and shipping details

Category	22499-SENSORS ACCESSORIES
Discount Schedule	DS2
GTIN	3389110197303
Returnability	No
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.92 in (12.5 cm)
Package 1 Width	9.84 in (25.0 cm)
Package 1 Length	9.84 in (25.0 cm)
Package 1 Weight	10.11 lb(US) (4.587 kg)
Unit Type of Package 2	S03
Number of Units in Package 2	2
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	21.32 lb(US) (9.672 kg)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[XZCB4L0100](#)