



Main

Range of Product	Telemecanique Cabling components
Accessory / separate part category	Cabling accessory
Accessory / Separate Part Type	Pre-wired connectors
Series name	Application

Complementary

Electrical connection	Straight female connector M12, 8 pins
Cable connector fixing	Screw-on
Collar material	Nickel plated brass
Status LED	Without
Cable length	32.81 ft (10 m)
Cable outer diameter	0.25 in (6.4 mm)
Cable composition	8 x 0.34 mm ²
Wire insulation material	PUR
[Ue] rated operational voltage	30 V AC 36 V DC
Line Rated Current	2 A
Contact resistance	5000 µOhm
Minimum insulating resistance	1 GΩ
Net Weight	1.04 lb(US) (0.47 kg)

Environment

IP Degree of Protection	IP69K IP67 IP65
Ambient Air Temperature for Storage	-40...194 °F (-40...90 °C)

Ordering and shipping details

Category	22499-SENSORS ACCESSORIES
Discount Schedule	DS2
GTIN	3389119028332
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.77 in (4.500 cm)
Package 1 Width	7.60 in (19.300 cm)
Package 1 Length	7.99 in (20.300 cm)
Package 1 Weight	18.98 oz (538.000 g)

Unit Type of Package 2	S02
Number of Units in Package 2	5
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	6.83 lb(US) (3.100 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------

Connections and Schemes

Connectors



GY : Grey
PK : Pink
VT : Violet
BN : Brown
OG : Orange
WH : White
BU : Blue
BK : Black

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[XZCP29P12L10](#)