

ZCKD05

Limit switch head, Limit switches XC Standard, ZCKD, without lever spring return left and or right actuation





Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKD
Head type	Rotary head
Product Compatibility	XCKS XCKM XCKL
Associated lever	ZCKY39 ZCKY33 ZCKY91 ZCKY43 ZCKY59 ZCKY54 ZCKY81 ZCKY31 ZCKY55 ZCKY41 ZCKY49 ZCKY34

Associated body	ZCKMD37H7 ZCKMD37H29 ZCKM1H29 ZCKL7H7 ZCKM1 ZCKL1 ZCKSD39H29 ZCKL8H7 ZCKSD37 ZCKM5H7 ZCKSD31H29 ZCKMD31H29 ZCKSD31 ZCKLD35H7 ZCKM6H29 ZCKLD31H7 ZCKMD37 ZCKLD39 ZCKS7 ZCKLD39H7 ZCKL1H7 ZCKM5 ZCKS404H29 ZCKMD39H29 ZCKS8 ZCKMD35 ZCKM9 ZCKS2 ZCKMD35H7 ZCKL7 ZCKM6 ZCKM8H7 ZCKL5 ZCKLD37H7 ZCKMD39H7 ZCKSD35H29 ZCKS7H29 ZCKS6H29 ZCKSD37H29 ZCKS1H29 ZCKL6 ZCKM9H29 ZCKM7 ZCKSD35 ZCKLD37 ZCKM7H29 ZCKS9H29 ZCKS9 ZCKMD31H7 ZCKS8H29 ZCKM6H7 ZCKM1H7 ZCKLD31 ZCKM8H29 ZCKS5 ZCKS1 ZCKL8 ZCKS2H29 ZCKL6H7 ZCKM7H7 ZCKL5H7 ZCKMD35H29 ZCKMD31 ZCKLD35 ZCKM8 ZCKMD39 ZCKS5H29 ZCKS6 ZCKM5H29 ZCKSD39
Movement of operating head	Rotary
Type of operator	Without operating lever spring return
Type of approach	Lateral approach, 1 or 2 programmable direction

Complementary

Switch actuation	From left and/or right CW and/or CCW
Positive opening	Without With
Head material	Plastic

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22416-LIMIT SWITCHES,IEC,XCKL
Discount Schedule	T
GTIN	3389110647037
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.52 in (6.400 cm)
Package 1 Width	1.34 in (3.400 cm)
Package 1 Length	3.03 in (7.700 cm)
Package 1 Weight	2.61 oz (74.000 g)
Unit Type of Package 2	S01
Number of Units in Package 2	28
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	5.91 in (15.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	5.19 lb(US) (2.356 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	896
Package 3 Height	30.31 in (77.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	178.81 lb(US) (81.108 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[ZCKD05](#)