



## Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKE
Head type	Multi-directional head
Product Compatibility	XCKJ
Associated body	ZCKJ21 ZCKJ6H7 ZCKJD35H7 ZCKJ11H7 ZCKJ1H7 ZCKJD37 ZCKJD35H29 ZCKJD35 ZCKJ21H7 ZCKJ11 ZCKJD31H29 ZCKJD39 ZCKJD31 ZCKJ7H7 ZCKJ5H7 ZCKJ9 ZCKJ9H7 ZCKJ2H29 ZCKJ21H29 ZCKJD37H7 ZCKJ6 ZCKJ11H29 ZCKJ8H7 ZCKJ1 ZCKJD39H7 ZCKJD37H29 ZCKJ2H7 ZCKJ9H29 ZCKJ5 ZCKJ6H29 ZCKJ7H29 ZCKJ5H29 ZCKJD39H29 ZCKJ2 ZCKJ8H29 ZCKJD31H7 ZCKJ1H29 ZCKJ7 ZCKJ8
Movement of operating head	Multi-directional
Type of operator	Cat's whisker spring return
Type of approach	Multi-directional approach

## Complementary

Switch actuation	By any moving part
Positive opening	Without
Net Weight	0.25 lb(US) (0.115 kg)
Head material	Metal

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Ambient Air Temperature for Operation	50...248 °F (10...120 °C)
Ambient Air Temperature for Storage	50...248 °F (10...120 °C)
Environmental characteristic	High temperature

## Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110599398
Nbr. of units in pkg.	1
Package weight(Lbs)	4.41 oz (125.0 g)
Returnability	No
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.46 in (3.7 cm)
Package 1 width	1.46 in (3.7 cm)
Package 1 Length	6.42 in (16.3 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	24
Package 2 Weight	7.33 lb(US) (3.324 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[ZCKE065](#)