

ZCKE06TK

Limit switch head, Limit switches XC Standard, ZCKE, cat's whisker, for XCKJ



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKE
Head type	Multi-directional head
Product Compatibility	XCKJ
Associated body	ZCKJ8H7 ZCKJD35H29 ZCKJ21H29 ZCKJD39 ZCKJ6 ZCKJ2H29 ZCKJ9 ZCKJD31 ZCKJ2H7 ZCKJ21 ZCKJ1H29 ZCKJ1 ZCKJ5 ZCKJ1H7 ZCKJD37 ZCKJ11H7 ZCKJD35 ZCKJ8H29 ZCKJ7 ZCKJD39H7 ZCKJ5H7 ZCKJ5H29 ZCKJ6H7 ZCKJ9H29 ZCKJ7H29 ZCKJ9H7 ZCKJD31H29 ZCKJD37H7 ZCKJD31H7 ZCKJ8 ZCKJ11 ZCKJD37H29 ZCKJ2 ZCKJD35H7 ZCKJ6H29 ZCKJ11H29 ZCKJ7H7 ZCKJD39H29 ZCKJ21H7
Movement of operating head	Multi-directional
Type of operator	Cat's whisker spring return
Type of approach	Multi-directional approach

Complementary

Switch actuation	By any moving part
Positive opening	Without
Head material	Metal

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Corrosive

Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110932942
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.46 in (3.7 cm)
Package 1 Width	1.50 in (3.8 cm)
Package 1 Length	6.42 in (16.3 cm)
Package 1 Weight	4.34 oz (123.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	60
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	17.27 lb(US) (7.835 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[ZCKE06TK](#)