



FEATURES:

- Miniature IC Test Tip fits directly over the test probe tip.
- The small size and recessed contact allow the IC Adapter to prove one leg of a DIP without shorting an adjacent leg.
- Plastic projections on either side of the contact tip slide between the DIP legs to hold adapter in place and prevent slipping.

MATERIALS:

Insulation: Nylon

Tip: Stainless steel

Color: Black, Red, Green

RATINGS:

Operating Temperature: +80°C. (+176°F.) Max

Operating Voltage: 300 VRMS/DC

Current: 3 Amperes.

ORDERING INFORMATION: Model 5246-*

*= Color, -0 Black, -2 Red, -5 Green Ordering Example: 5246-2 Adapter Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5246-2](#) [5246-5](#) [5246-0](#)