



[Article Page](#)

Product Description  
 Name  
 Order number  
 Switching distance  
 Mounting


capacitive sensor DC  
 SC3-M8MN45-DPS  
 08323080310  
 3 mm

 non shielded


Switch type

 N.O.  
 DC PNP

Signal Type  
 Connection

 Cable

Connection diagramm



fine-pitch thread M8 x 45

Dimension (in mm)  
 Technical Specification

Operating voltage  
 Max. ripple  
 Voltage drop  
 Max. load current  
 No load current  
 Leakage current  
 Switching frequency  
 Switching hysteresis  
 Operating temperature  
 Temperature drift  
 Repeat accuracy  
 Switching state  
 Digital output  
 Short-circuit proof  
 Overload protection  
 Reverse voltage protection  
 Protection category  
 EMC-level  
 Material active face  
 Termination

10 - 30 VDC  
 $\leq 10 \%$   
 2 V  
 200 mA  
 $\leq 10 \text{ mA}$   
 $\leq 10 \mu\text{A}$   
 100  
 $\leq 15 \%$   
 -25 ° C to 70 ° C  
 $\leq 10 \%$   
 $\leq 5 \%$   
 LED  
 yes  
 yes  
 yes  
 IP67  
 DIN EN 60947-5-2:2008  
 POM  
 2m PUR 3x0,15 mm<sup>2</sup>

**Errors and omissions exceptet**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[08323080310](#)