


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 3230: UPDATE DWG FORMAT	3/18/08	D.GRIFFIN
F	ECN 6519: UPDATED FORMAT, PACKAGING, AND LOGOS	11/19/12	D. DESJARDIN



LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CC58C- <u>XXX</u>	WHERE XXX = LENGTH IN FEET	CC58C-1.5 (1.5 FEET) CC58C-12 (12 FEET)

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13] PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY MCCORMICK	05/03/01		
	CHECKED BY D.PARHAM	06/06/01	CATEGORY COAXIAL	
	APPROVED BY R.CARRICK	06/11/01	PRODUCT DESCRIPTION CA BNC M/BNC M RG58C/U	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. CC58C	REV. F
		SCALE: NONE	CAD FILE: CC58C.SLDDRW	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[infinite Electronics:](#)

[CC58C-6](#) [CC58C-10](#) [CC58C-12](#) [CC58C-1.5](#) [CC58C-2](#) [CC58C-100](#) [CC58C-50](#) [CC58C-7.5](#) [CC58C-15](#) [CC58C-25](#)
[CC58C-3](#) [CC58C-5](#) [CC58C-4](#) [CC58C-1](#)