



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/7/12	D.GRIFFIN
B	ECN6549: ADDED CHANNEL RATING NOTE	2/11/13	D. DESJARDIN
C	ECN 7667: REMOVE CHANNEL RATING NOTE AND ALL LENGTHS OVER 30 FT	11/18/14	D.FRISIELLO



- NOTES:**
1. PLUG CONFORMS TO TIA-1096
 2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
- REGULATORY COMPLIANCE:**
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13] PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY D. DESJARDIN	3/2/12		CATEGORY TELECOM/MODULAR	
	CHECKED BY J. RUST	3/6/12			
	APPROVED BY D. GALLAGHER	3/6/12			
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			PRODUCT DESCRIPTION C5E PVC FTP LFT-DWN		
COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321	DWG. NO. TRD815SRA11	REV. C
		SCALE: NONE	CAD FILE: TRD815SRA11.SLDDRW		SHEET 1 OF 2

8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD815SRA11BLK-1	BLACK	1.0 [0.30]	TRD815SRA11RD-1	RED	1.0 [0.30]	TRD815SRA11GRY-1	GRAY	1.0 [0.30]	TRD815SRA11Y-1	YELLOW	1.0 [0.30]
TRD815SRA11BLK-2	BLACK	2.0 [0.61]	TRD815SRA11RD-2	RED	2.0 [0.61]	TRD815SRA11GRY-2	GRAY	2.0 [0.61]	TRD815SRA11Y-2	YELLOW	2.0 [0.61]
TRD815SRA11BLK-3	BLACK	3.0 [0.91]	TRD815SRA11RD-3	RED	3.0 [0.91]	TRD815SRA11GRY-3	GRAY	3.0 [0.91]	TRD815SRA11Y-3	YELLOW	3.0 [0.91]
TRD815SRA11BLK-5	BLACK	5.0 [1.52]	TRD815SRA11RD-5	RED	5.0 [1.52]	TRD815SRA11GRY-5	GRAY	5.0 [1.52]	TRD815SRA11Y-5	YELLOW	5.0 [1.52]
TRD815SRA11BLK-7	BLACK	7.0 [2.13]	TRD815SRA11RD-7	RED	7.0 [2.13]	TRD815SRA11GRY-7	GRAY	7.0 [2.13]	TRD815SRA11Y-7	YELLOW	7.0 [2.13]
TRD815SRA11BLK-10	BLACK	10.0 [3.05]	TRD815SRA11RD-10	RED	10.0 [3.05]	TRD815SRA11GRY-10	GRAY	10.0 [3.05]	TRD815SRA11Y-10	YELLOW	10.0 [3.05]
TRD815SRA11BLK-15	BLACK	15.0 [4.57]	TRD815SRA11RD-15	RED	15.0 [4.57]	TRD815SRA11GRY-15	GRAY	15.0 [4.57]	TRD815SRA11Y-15	YELLOW	15.0 [4.57]
TRD815SRA11BLK-20	BLACK	20.0 [6.10]	TRD815SRA11RD-20	RED	20.0 [6.10]	TRD815SRA11GRY-20	GRAY	20.0 [6.10]	TRD815SRA11Y-20	YELLOW	20.0 [6.10]
TRD815SRA11BLK-25	BLACK	25.0 [7.62]	TRD815SRA11RD-25	RED	25.0 [7.62]	TRD815SRA11GRY-25	GRAY	25.0 [7.62]	TRD815SRA11Y-25	YELLOW	25.0 [7.62]
TRD815SRA11BLK-30	BLACK	30.0 [9.14]	TRD815SRA11RD-30	RED	30.0 [9.14]	TRD815SRA11GRY-30	GRAY	30.0 [9.14]	TRD815SRA11Y-30	YELLOW	30.0 [9.14]
TRD815SRA11BL-1	BLUE	1.0 [0.30]	TRD815SRA11GR-1	GREEN	1.0 [0.30]	TRD815SRA11OR-1	ORANGE	1.0 [0.30]			
TRD815SRA11BL-2	BLUE	2.0 [0.61]	TRD815SRA11GR-2	GREEN	2.0 [0.61]	TRD815SRA11OR-2	ORANGE	2.0 [0.61]			
TRD815SRA11BL-3	BLUE	3.0 [0.91]	TRD815SRA11GR-3	GREEN	3.0 [0.91]	TRD815SRA11OR-3	ORANGE	3.0 [0.91]			
TRD815SRA11BL-5	BLUE	5.0 [1.52]	TRD815SRA11GR-5	GREEN	5.0 [1.52]	TRD815SRA11OR-5	ORANGE	5.0 [1.52]			
TRD815SRA11BL-7	BLUE	7.0 [2.13]	TRD815SRA11GR-7	GREEN	7.0 [2.13]	TRD815SRA11OR-7	ORANGE	7.0 [2.13]			
TRD815SRA11BL-10	BLUE	10.0 [3.05]	TRD815SRA11GR-10	GREEN	10.0 [3.05]	TRD815SRA11OR-10	ORANGE	10.0 [3.05]			
TRD815SRA11BL-15	BLUE	15.0 [4.57]	TRD815SRA11GR-15	GREEN	15.0 [4.57]	TRD815SRA11OR-15	ORANGE	15.0 [4.57]			
TRD815SRA11BL-20	BLUE	20.0 [6.10]	TRD815SRA11GR-20	GREEN	20.0 [6.10]	TRD815SRA11OR-20	ORANGE	20.0 [6.10]			
TRD815SRA11BL-25	BLUE	25.0 [7.62]	TRD815SRA11GR-25	GREEN	25.0 [7.62]	TRD815SRA11OR-25	ORANGE	25.0 [7.62]			
TRD815SRA11BL-30	BLUE	30.0 [9.14]	TRD815SRA11GR-30	GREEN	30.0 [9.14]	TRD815SRA11OR-30	ORANGE	30.0 [9.14]			



45 BEECHWOOD DRIVE
NORTH ANDOVER, MA
01845

CATEGORY
TELCOM/MODULAR

PRODUCT DESCRIPTION
C5E PVC FTP LFT-DWN

SIZE
A

FSCM NO.
43321

DWG. NO.
TRD815SRA11

REV.
C

SCALE: NONE | CAD FILE: TRD815SRA11.SLDDRW | SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[infinite Electronics:](#)

[TRD815SRA11Y-5](#) [TRD815SRA11BL-10](#) [TRD815SRA11BL-5](#) [TRD815SRA11BLK-25](#) [TRD815SRA11GR-3](#)
[TRD815SRA11Y-25](#) [TRD815SRA11GR-20](#) [TRD815SRA11OR-7](#) [TRD815SRA11Y-30](#) [TRD815SRA11BLK-2](#)
[TRD815SRA11Y-20](#) [TRD815SRA11BL-1](#) [TRD815SRA11GRY-20](#) [TRD815SRA11BL-20](#) [TRD815SRA11RD-25](#)
[TRD815SRA11OR-1](#) [TRD815SRA11GR-25](#) [TRD815SRA11GR-30](#) [TRD815SRA11BLK-7](#) [TRD815SRA11GR-10](#)
[TRD815SRA11GRY-3](#) [TRD815SRA11RD-2](#) [TRD815SRA11GR-5](#) [TRD815SRA11GRY-10](#) [TRD815SRA11OR-25](#)
[TRD815SRA11BL-2](#) [TRD815SRA11Y-15](#) [TRD815SRA11GR-7](#) [TRD815SRA11OR-30](#) [TRD815SRA11OR-5](#)
[TRD815SRA11BLK-3](#) [TRD815SRA11BLK-10](#) [TRD815SRA11BLK-15](#) [TRD815SRA11GRY-1](#) [TRD815SRA11OR-20](#)
[TRD815SRA11Y-10](#) [TRD815SRA11BL-3](#) [TRD815SRA11BL-25](#) [TRD815SRA11OR-3](#) [TRD815SRA11RD-30](#)
[TRD815SRA11BLK-30](#) [TRD815SRA11GR-1](#) [TRD815SRA11GRY-5](#) [TRD815SRA11BLK-1](#) [TRD815SRA11GRY-25](#)
[TRD815SRA11OR-15](#) [TRD815SRA11GRY-30](#) [TRD815SRA11RD-10](#) [TRD815SRA11GRY-2](#) [TRD815SRA11RD-5](#)
[TRD815SRA11Y-7](#) [TRD815SRA11GR-2](#) [TRD815SRA11BL-15](#) [TRD815SRA11GRY-15](#) [TRD815SRA11RD-7](#)
[TRD815SRA11Y-3](#) [TRD815SRA11BLK-20](#) [TRD815SRA11Y-1](#) [TRD815SRA11OR-10](#) [TRD815SRA11RD-1](#)
[TRD815SRA11RD-15](#) [TRD815SRA11Y-2](#) [TRD815SRA11GR-15](#) [TRD815SRA11GRY-7](#) [TRD815SRA11RD-3](#)
[TRD815SRA11RD-20](#) [TRD815SRA11BL-30](#) [TRD815SRA11BL-7](#) [TRD815SRA11BLK-5](#) [TRD815SRA11OR-2](#)