


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/1/11	D.GRIFFIN
-	-	-	-

"P1"  
RJ45 (8X8)  
UNSHIELDED MALE  
GOLD PLATED PINS



"J1"  
RJ45 (8X8)  
UNSHIELDED FEMALE  
GOLD PLATED CONTACTS

(4) UNSHIELDED TWISTED PAIRS,  
CAT5e MODULAR CABLE,  
CONDUCTORS: 24AWG STRANDED COPPER  
OUTER JACKET: PVC, GRAY (RAL #7044)



PART NUMBER	LENGTH	
	FEET	[METERS]
TRDC5EXT-3	3.0	[.91]
TRDC5EXT-5	5.0	[1.52]
TRDC5EXT-7	7.0	[2.13]
TRDC5EXT-10	10.0	[3.05]
TRDC5EXT-15	15.0	[4.57]
TRDC5EXT-25	25.0	[7.62]

NOTES:

1. MODULAR CONNECTOR TO MEET TIA-1096.
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005 PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D. CASTRO	1/25/11		
	CHECKED BY D. PARHAM	1/26/11	CATEGORY TELECOM/MODULAR	
	APPROVED BY D. GALLAGHER	1/31/11	PRODUCT DESCRIPTION CA C5E RJ45 M/F UTP NON FLANGED EXTENSION	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. TRDC5EXT
COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: TRDC5EXT.SLDDRW	REV. <b>A</b>
REF		SHEET 1 OF 1		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[infinite Electronics:](#)

[TRDC5EXT-10](#) [TRDC5EXT-3](#) [TRDC5EXT-15](#) [TRDC5EXT-25](#) [TRDC5EXT-5](#) [TRDC5EXT-7](#)