



Shield

1	White/orange
2	Orange
3	White/green
4	Green
5	White/brown
6	Brown
7	White/blue
8	Blue



6.0 to 100	±1%
0.6 to 5.9	+0.04
0.2 to 0.5	+0.02
a [m]	tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.5	XXX=005
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
step	a[m]	XXX

RJI Cable 4x2xAWG 24/7, EtherRail, CAT7, black	21330700853XXX
Type of cable	Part no.

		All Dimensions in mm Original Size DIN A3		Scale 2:1	Free size tol.		Ref.								
							Sub.								
		All rights reserved		Created by BALSAN		Inspected by FARCASIU		Standardisation ROEBEN		Date 2021-10-06		State Final Release			
Department EL PD				Title har-speed M12 flying cable D=8,1								Doc-Key / ECM-Nr. 100605359/UGD/000/F 500000203232			
HARTING D-32339 Espelkamp				Type TB		Number 21330700853XXX						Rev. F		Pag. 1/	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21330700853030](#)