



- easy handling
- straight action principle
- ratchet release
- contact positioning with flap locator type FC
- precisely ground profiles
- burnished surface
- ergonomically formed soft grips
- colour: rape yellow/signal black
- fully recyclable; RoHS complied
- application range: FC3 contacts
- wire gauge: profile 1: 0,5-1,3mm<sup>2</sup>
- profile 2: 1,0-1,5mm<sup>2</sup>
- weight approx. 610 g

for FC3 crimp contacts:					
09 06 000 9572	male	2	0,5-1,5	20-16	1,6-2,8
09 06 000 9552	male	1	0,5-1,5	20-16	1,6-2,8
09 06 000 8482	female	2	0,5-1,5	20-16	1,6-2,8
09 06 000 8472	female	1	0,5-1,5	20-16	1,6-2,8
09 06 000 6462	female	Sn	0,5-1,5	20-16	1,6-2,8
contact no.	male / female	PL	wire gauge	AWG	InsulationØ

	All rights reserved Department EL PD	All Dimensions in mm Original Size DIN A3		Scale 1:1	Free size tol.	Ref. Sub.
		Created by WAERMKER	Inspected by HAERTLING	Standardisation HOFFMANN	Date 2020-05-07	State Final Release
HARTING Electronics GmbH D-32339 Espelkamp		Title Crimpset FC3		Type TB	Number 09990000773	Rev. A
						Page 1/1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[9990000773](#)