

Han TC70 M-contact 10mm² protected




Image is for illustration purposes only. Please refer to product description.

Part number	09 11 000 7100
Specification	Han TC70 M-contact 10mm ² protected
HARTING eCatalogue	https://b2b.harting.com/09110007100

Identification

Category	Contacts
Series	TC 70
Type of contact	Crimp contact

Version

Gender	Male
Manufacturing process	Turned contacts
Details	Finger safe

Technical characteristics

Conductor cross-section	10 mm ²
Rated current	≤70 A
Contact resistance	≤0.5 mΩ
Stripping length	15.5 mm
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Pushing Performance
Since 1945

Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	10
Net weight	5 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140188099
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09110007100](#) [9110007100](#)