

SEK CAB FLAT NSH RND AWG28/7 37P 100m



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 037 7011
Specification	SEK CAB FLAT NSH RND AWG28/7 37P 100m
HARTING eCatalogue	https://b2b.harting.com/09180377011

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (round)

Version

Cable length	100 m
Number of cores	37
Core structure	AWG 28/7

Technical characteristics

Limiting temperature	-30 ... +105 °C unmoved -20 ... +105 °C moved
Conductor resistance @ 20 °C	≤225 Ω/km
Signal run time @ 20 °C	≤5.25 ns/m
Impedance @ 100 MHz	75 Ω

Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance

Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Commercial data

Packaging size	1
Net weight	1 g
Country of origin	USA
European customs tariff number	85444993
eCl@ss	27061801 Data and communication cable (copper)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09180377011](#)