

Han PP Power L metal housing



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 014 0301
Specification	Han PP Power L metal housing
HARTING eCatalogue	https://b2b.harting.com/09350140301

Identification

Category	Connectors
Series	Han [®] PushPull (V14)
Type of hood/housing	Bulkhead mounted housing

Version

Locking type	PushPull
--------------	----------

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
California Proposition 65 substances	Nickel
California Proposition 65 substances	Naphthalene

Specifications and approvals

Specifications	IEC/PAS 61076-3-126
UL / CSA	UL 1059 XCFR2.E314677 CSA-C22.2 No. 158-10 XCFR8.E314677

Commercial data

Packaging size	1
Net weight	21.667 g
Country of origin	Vietnam
European customs tariff number	85389099
GTIN	5713140224094
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09350140301](#) [9350140301](#)