



Pushing Performance  
Since 1945

# RJ45 RJ45 10G Cat6, IP65 plug repair set



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 100 1561
Specification	RJ45 RJ45 10G Cat6, IP65 plug repair set
HARTING eCatalogue	<a href="https://b2b.harting.com/09451001561">https://b2b.harting.com/09451001561</a>

## Identification

Category	Connectors
Series	RJ45
Element	Cable connector
Specification	RJ45 Spare part

## Version

Termination method	IDC termination
Size	3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Pack contents	Connector insert

## Technical characteristics

Conductor cross-section	0.1 ... 0.32 mm² Stranded 0.22 ... 0.32 mm² Solid
Conductor cross-section	AWG 27/7 ... AWG 22/7 Stranded AWG 27/1 ... AWG 22/1 Solid
Wire outer diameter	1.6 mm
Transmission characteristics	Cat. 6 Class E <sub>A</sub> up to 500 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s



**Pushing Performance**  
Since 1945

## Technical characteristics

Limiting temperature	-40 ... +70 °C
Cable diameter	6.5 ... 9.5 mm

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide
	Lead
	Nickel

## Specifications and approvals

Approvals	DNV GL
PROFINET	Yes

## Commercial data

Packaging size	1
Net weight	15 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140058705
ETIM	EC000438
eCl@ss	27440205 Contact insert for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09451001561](#)