

## har-button ring illumination



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 453 2101
Specification	har-button ring illumination
HARTING eCatalogue	<a href="https://b2b.harting.com/09454532101">https://b2b.harting.com/09454532101</a>

### Identification

Category	Operator interfaces
Series	har-button
Element	Push buttons
Specification	with ring illumination

### Version

Diameter of the mounting hole	30.5 mm
Details	This item requires additional contact blocks, a module holder, and a protective cap. Please select these under "Matching Products".

### Technical characteristics

Actuation path	6 mm
Overvoltage category	III (protection by low voltage)
Tightening torque	≤2.5 Nm Fixing nut
Operating temperature	-40 ... +70 °C
Storage temperature	-50 ... +85 °C
Degree of protection acc. to IEC 60529	IP69 / IPX9K acc. to ISO 20653
Isolation group	I (600 ≤ CTI)
Thickness of the panel	1 ... 8 mm

### Material properties

Colour	silver
--------	--------



**Pushing Performance**  
Since 1945

## Specifications and approvals

Specifications	EN 60947-5-1
UL / CSA	UL 60947-5-1 NKCR.E534795
	CSA C22.2 No. 60947-5-1:22 NKCR7.E534795
	UL 60947-1 NKCR.E534795
	CSA C22.2 No. 60947-1:22 NKCR7.E534795

## Commercial data

Packaging size	10
Net weight	22.89 g
Country of origin	Germany
European customs tariff number	85365080
GTIN	5713140449831
ETIM	EC000221

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09454532101](#)