

Han CGM-P-EXi M20 D 5...9mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 7101
Specification	Han CGM-P-EXi M20 D 5...9mm
HARTING eCatalogue	https://b2b.harting.com/19000007101

Identification

Category	Accessories
Series of hoods/housings	Han [®] CGM-Ex i
Type of accessory	Cable gland

Version

Field of application	Intrinsically safe electric circuits
----------------------	--------------------------------------

Technical characteristics

Tightening torque	≤4.5 Nm (depending on the cable and the seal insert used)
Wrench size	24
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M20
Clamping range	5 ... 9 mm
Width across corners	26.4 mm

Material properties

Material (cable glands)	Polyamide (PA)
Colour (cable gland)	RAL 5012 (light blue) RAL 9005 (jet black)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	18 g
Country of origin	Germany
European customs tariff number	39269097
GTIN	5713140192836
ETIM	EC000441
eCl@ss	27140802 Screwed cable gland (explosion-proof, electrical)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[1900007101](#)