

## Han 6EMC/B-HTE-HC-for SL-M32-HMC



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 206 0447
Specification	Han 6EMC/B-HTE-HC-for SL-M32-HMC
HARTING eCatalogue	<a href="https://b2b.harting.com/19622060447">https://b2b.harting.com/19622060447</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> EMC/B
Type of hood/housing	Hood

### Version

Size	6 B
Version	Top entry
Cable entry	1x M32
Locking type	Single locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles with other HMC components	≥10,000
Degree of protection acc. to IEC 60529	IP65 IP66
Type rating acc. to UL 50 / UL 50E	4 12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted



**Pushing Performance**  
Since 1945

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	128.4 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140171534
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19622060447](#)