



Pushing Performance
Since 1945

FO CA LCdx-LCdx 2E9/125 G657.A1, 20.0m




Image is for illustration purposes only. Please refer to product description.

Part number	33 01 241 0200 008
Specification	FO CA LCdx-LCdx 2E9/125 G657.A1, 20.0m
HARTING eCatalogue	https://b2b.harting.com/33012410200008

Identification

Category	System cabling
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	LC duplex
Connector 2	LC duplex
Type of cable	FO cable
Description of the cable	Singlemode

Version

Cable length	20 m
Number of fibres	2
Fiber type	2E9/125 G657.A1

Technical characteristics

Cable diameter	5.17 mm
----------------	---------

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol
ECHA SCIP number	8a5c37c3-d5dc-469f-b994-a066c654819f
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Net weight	396 g
Country of origin	Latvia
European customs tariff number	85447000
GTIN	5713140149762
eCl@ss	27061003 Patch cable fiber-optic

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33012410200008](#)