



Pushing Performance  
Since 1945

# ix Type A OM Profinet C PUR 5.0m



Image is for illustration purposes only. Please refer to product description.

Part number	33 48 313 1412 050
Specification	ix Type A OM Profinet C PUR 5.0m
HARTING eCatalogue	<a href="https://b2b.harting.com/33483131412050">https://b2b.harting.com/33483131412050</a>

## Identification

Category	System cabling
Series	HARTING ix Industrial®
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING ix Industrial® PushPull IP20
	Type A
	Overmoulded
	IDC termination
Connector 2	HARTING ix Industrial® PushPull IP20
	Type A
	Overmoulded
	IDC termination
Type of cable	Copper cable (round)

## Version

Cable length	5 m
Number of cores	4
Core structure	4x AWG 22/7
Number of contacts	10

## Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s



Pushing Performance  
Since 1945

Technical characteristics

Limiting temperature	-40 ... +70 °C unmoved
	-20 ... +60 °C moved

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Green

Specifications and approvals

Specifications	IEC 60332-1-2 Flame retardancy
	UN/ECE-R 118 fire protection for rolling stock
PROFINET	Yes

Commercial data

Packaging size	1
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140330726
eCl@ss	27061801 Data and communication cable (copper)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33483131412050](#)