

ix Type A OM - DB RJ45 Cat.6A PVC 3.0m



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 33 48 314 7805 030 |
| Specification | ix Type A OM - DB RJ45 Cat.6A PVC 3.0m |
| HARTING eCatalogue | https://b2b.harting.com/33483147805030 |

Identification

| | |
|---------------|--|
| Category | System cabling |
| Series | HARTING ix Industrial® |
| Element | Cable assemblies |
| Specification | Pre-assembled on both sides |
| Connector 1 | HARTING ix Industrial® PushPull IP20 Type A Overmoulded IDC termination |
| Connector 2 | HARTING DualBoot RJ45 |
| Type of cable | Copper cable (round) |

Version

| | |
|--------------------|----------------|
| Cable length | 3 m |
| Number of cores | 8 |
| Core structure | 4x 2x AWG 26/7 |
| Number of contacts | 8 |

Technical characteristics

| | |
|------------------------------|--|
| Transmission characteristics | Cat. 6 _A Class E _A up to 500 MHz |
| Data rate | 10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s |



Pushing Performance
Since 1945

Technical characteristics

| | |
|----------------------|------------------------|
| Limiting temperature | -20 ... +80 °C unmoved |
| | -10 ... +70 °C moved |

Material properties

| | |
|--------------------------------------|---------------|
| Material (cable) | PVC |
| Colour (cable) | Yellow |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Not contained |

Specifications and approvals

| | |
|----------------|--|
| Specifications | IEC 60332-1-2 Flame retardancy |
| | IEC 61076-3-124 |
| | UN/ECE-R 118 fire protection for rolling stock |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Country of origin | Latvia |
| European customs tariff number | 85444290 |
| GTIN | 5713140332768 |
| eCl@ss | 27060390 Ready-made data cable (unspecified) |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33483147805030](#)