

## Han1A CA 12 Pole -lever m/- PVC 10m



Image is for illustration purposes only. Please refer to product description.

Part number	33 50 140 0304 100
Specification	Han1A CA 12 Pole -lever m/- PVC 10m
HARTING eCatalogue	<a href="https://b2b.harting.com/33501400304100">https://b2b.harting.com/33501400304100</a>

### Identification

Category	System cabling
Series	Han <sup>®</sup> 1A
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	Han <sup>®</sup> 1A Male
Type of cable	Copper cable (round)
Description of the cable	Oil resistant

### Version

Cable length	10 m
Number of cores	12
Core structure	12x 0.34 mm <sup>2</sup>
Number of contacts	12
Locking type	Single locking lever

### Technical characteristics

Rated current	6.5 A
Rated voltage	50 V
Limiting temperature	-30 ... +80 °C unmoved -5 ... +80 °C moved
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65



**Pushing Performance**  
Since 1945

## Technical characteristics

Cable diameter	7.8 mm
----------------	--------

## Material properties

Material (cable)	PVC
Colour (cable)	Grey

## Specifications and approvals

Specifications	IEC 60332-1-2 Flame retardancy
----------------	--------------------------------

## Commercial data

Packaging size	1
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140237513
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33501400304100](#)