

Han1A CA 12 Pole +latch m/- PVC 5m



Image is for illustration purposes only. Please refer to product description.

Part number	33 50 160 0304 050
Specification	Han1A CA 12 Pole +latch m/- PVC 5m
HARTING eCatalogue	https://b2b.harting.com/33501600304050

Identification

Category	System cabling
Series	Han [®] 1A
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	Han [®] 1A Male
Type of cable	Copper cable (round)
Description of the cable	Oil resistant

Version

Cable length	5 m
Number of cores	12
Core structure	12x 0.34 mm ²
Number of contacts	12
Locking type	Snap-in latches

Technical characteristics

Rated current	6.5 A
Rated voltage	50 V
Limiting temperature	-30 ... +80 °C unmoved -5 ... +80 °C moved
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65



Pushing Performance
Since 1945

Technical characteristics

Cable diameter	7.8 mm
----------------	--------

Material properties

Material (cable)	PVC
Colour (cable)	Grey

Specifications and approvals

Specifications	IEC 60332-1-2 Flame retardancy
----------------	--------------------------------

Commercial data

Packaging size	1
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140237544
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33501600304050](#)