







NOTES:

- METALSHELLS: STEEL; YELLOW CHROMATE
- INSULATORS: PBT GF UL 94 V-0, GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: 30µin HARD GOLD over min. 50µin NICKEL
- HIGH POWER CONTACTS 15A: COPPER ALLOY
PLATING MATING AREA: 30µin HARD GOLD over min. 50µin NICKEL
PLATING TERMINATION SIDE: 160-240µin TIN over 80µin NICKEL
- THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- METAL BRACKET: ZINC DIE CAST; 300µin COPPER/40-120µin NICKEL/120-200µin TIN
- PCB-SNAP: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB HOLE: $\varnothing 3,1 \pm 0,1$; PCB THICKNESS 1,6mm
- P.C.B. HOLE DRILLINGS ON SHEET 2
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: **CFM21WA4P5-0394 CONEC ABC**



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND				tolerance		 dim. in mm	scale: 2:1 (5:1)		
								material: SEE NOTES		
					date	name	title: D-SUB COMBINATION MALE 90° 21WA4P with threaded insert,metal bracket and snap			
					drawn	02.04.13				Schmidt
					appd.	02.04.13				Koch
					norm					
					d-old			dwg no: 13K1A4277		DIN-A3 sh: 1
	a	Original						part no: CFM21WA4P5-0394		
	rev.	description	date	name						



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm		scale: 3:1					
								material: SEE SHEET 1					
									date		name	title: P.C.B. HOLE DRILLINGS D-SUB COMBINATION MALE 90° 21WA4P with threaded insert,metal bracket and snap	
								drawn	02.04.13		Schmidt		
								appd.	02.04.13		Koch		
								norm					
								d-old			dwg no:		DIN-A3
				a	Original					13K1A4277		sh: 2	
				rev.	description	date	name			part no: SEE SHEET 1			
				DO NOT ALTER CAD DRAWING BY HAND									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CFM21WA4P5-0394](#)