







THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN16B0005-009	2016/11/01	Yulong_wang	Change the Note.



- Note:
- * $\varnothing$ Important Dimension.
 - * Waterproof Rate: IP68.
 - * Housing: Nylon+GF, Black.
 - * $\triangle$ Female Pin: Copper Alloy, Gold Plated.
 - * Shell: Metal, Nickel Plated.
 - * Ground Lug: Copper Alloy, Nickel Plated.
 - * Screw Nut: Copper Alloy, Nickel Plated.
 - * Panel O-Ring: Viton, Green.
 - * Housing O-Ring: Viton, Green.
 - * Rated Voltage: 2 & 3Pin 60V dc. or ac.
4 ~ 6Pin 30V dc. or ac.
 - * $\triangle$ Rated Current: 2 ~ 4Pin 3A
5 & 6Pin 1.5A
 - * Operating Temperature: -20~+85°C
 - * For Panel Thickness: Min=2.0mm, Max=4.5mm.
 - * For PCB Thickness: Max=1.6mm.
 - * Recommended Nut Torque: 4~6kgf.cm.



Recommended
Panel Cut-Out

UNIT:mm		TITLE		M8 Female Conn. Panel 90° PCB Type w/Key Shielded		ITEM NO		DRAWN BY		DATE	
TOLERANCE		SCALE	SIZE	SHEET	OF	DWG NO		CHECKED BY		DATE	
.X ±0.25		2:1	A4	1	2	M8AS-XXPFFR-SF8001		Jinhai		2016-11-01	
.XX ±0.1		REV.	WC-REV.	QC: Inspection item		CUSTOMER		APPROVED BY		DATE	
.XXX ±0.05		B	A.6			ALTW		Jerry		2016-11-01	
ANGLES ±1°											

Amphenol LTW
安費諾亮泰企業股份有限公司

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL

F

E

M 8AS - XX P F F R - S F 8 001

8AS:M8 Sensor Shielded(w/Key)

02:2Pin

03:3Pin

04:4Pin

05:5Pin

06:6Pin

P:Panel(板端)

F:Female Connector(母座)

001:Phantom(虛擬料號)

8:IP68(防水等級68)



F:Front Fasten(前鎖式/Enclosure Rear Mount)

S:Screw(螺紋式)

R:90° PCB THT/DIP Type(90° 基板插件式)

F:Female Pin(母Pin) 



[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[M8AS-04PFFR-SF8001](#) [M8AS-03PFFR-SF8001](#) [M8AS-05PFFR-SF8001](#) [M8AS-02PFFR-SF8001](#) [M8AS-06PFFR-SF8001](#)