





REVISIONS				
REV	ECO	DESCRIPTION	DATE	BY APPR
A1	-	RELEASED DRAWING	Nov-9-17	Rookie Tommy
A2	-	ADD THE G5 PART NUMBER	Jan-28-19	Blink Tommy
A3	-	CHANGE HAND CRIMPER	Nov-8-19	Flan Tommy



CONTACT ORIENTATION ON ROLL
 NOTES: (UNLESS OTHERWISE SPECIFIED)

- MATERIAL:
 - CONTACT BODY: COPPER ALLOY.
 - OUTER SPRING: STAINLESS STEEL.
- SPECIFICATIONS:
 - CURRENT RATING: 5A MAX.
 - TERMINATION TYPE: CRIMPING.
 - WIRE RANGE: 30~28AWG.
 - WIRE INSULATION DIA(MAX): $\varnothing 1.8\text{mm}$.
- ROHS COMPLIANT.
- ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- AVAILABLE TOOLS:
 - HAND CRIMPER: MF-X-3958. ^(A3)
 - CRIMP APPLICATOR: MF-X-3957.
 - EXTRACTION TOOL: QXRT20.

P/N	CONTACT PLATING(MATING AREA)
SS28W2T	TIN PLATING OVER NICKEL.
SS28W2N	NICKEL PLATING OVER COPPERIZE.
SS28W2F	GOLD FLASH PLATING OVER NICKEL.
SS28W2G5	5 μ " GOLD PLATING OVER NICKEL.
SS28W2G10	10 μ " GOLD PLATING OVER NICKEL.
SS28W2G15	15 μ " GOLD PLATING OVER NICKEL.
SS28W2G30	30 μ " GOLD PLATING OVER NICKEL.



QUANTITY	PART NUMBER	DESCRIPTION	ITEM
		MATERIALS LIST	

UNLESS OTHERWISE SPECIFIED			
1) All dimensions are in millimeters.	DRAWN: Ril	DATE: Nov-8-19	Amphenol Sine Systems - www.amphenol-sine.com 44724 Montley Drive Clinton Township, MI 48038
2) Tolerances are as follows:	CHECKED: MWh	DATE: Nov-8-19	
3) Note reference =	ENGINEER:	APPROVE: Tommy	
4) Note reference =	CUSTOMER:	DATE: Nov-8-19	
5) Note reference =	APPROVE:		

PROCESS SPECIFICATIONS		MATERIAL SPECIFICATIONS		NEXT ASBY	
SIZE	TYPE	SIZE	TYPE	SCALE	NONE
B	C-	B	C-	SCALE	NONE
ECO-MATE SOCKET CONTACT, STAMPED, 28-30AWG, SIZE 20		ECO-MATE SOCKET CONTACT, STAMPED, 28-30AWG, SIZE 20		SHEET	1 OF 1
DRAWING NO. SS28W2XX		DRAWING NO. SS28W2XX		REVISION	A3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SS28W2G30](#)