


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Cable ②

8AP-04AMMM-SR7000 ①
Color: Black

8AP-04AMMM-SR7AXX
 XX: 01~99Meters
 01: 01Meter
 02: 02Meter
 ...
 99: 99Meters
 Cable Length(L): 01~99Meters



Pin Assignments
Front View

Pin	Wire Color	Pin Out
4	Black 黑	
3	Blue 藍	
2	White 白	
1	Brown 棕	
Conn.	Wire Color	

- Note:
- * \varnothing Important Dimension.
 - * Waterproof Rate: IP67.
 - * Connector: PU, Black.
 - * Male Pin: Copper Alloy, Gold Plated.
 - * Screw Nut: Nylon+GF, Black.
 - * Cable: UL2464 22AWG*4C+Talcum, PVC Jacket, UV Resistant, OD=5.0, Black.
 - * Cable Length Tolerance: 01M: ± 40 mm
 02~05M: ± 60 mm
 06~10M: ± 100 mm
 11~30M: ± 200 mm
 31~99M: ± 500 mm

UNIT:mm TOLERANCE ± 0.5 mm	TITLE M8 4Pin Cable M Conn. M Pin			ITEM NO 8AP-04AMMM-SR7AXX		DRAWN BY Mila		DATE 2014-01-09	
	SCALE 9:5	SIZE A4	SHEET 1 OF 1	DWG NO 8AP-04AMMM-SR7AXX		CHECKED BY Jimmy		DATE 2014-01-09	
	REV. A	WC-REV. A.2	\varnothing : Inspection item	CUSTOMER ALTW		APPROVED BY Jerry		DATE 2014-01-09	

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8AP-04AMMM-SR7A04](#)