






D see data sheet cable

Technical specification:

Rated voltage: IEC 61076-2-101	8pos 30 V
Current rating: IEC 61076-2-101	2 A at 40°C
Insulation resistance: IEC 60512	≥ 100 M Ω
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	≥ 100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Sealing:	FPM
Coupling nut:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey


Installation specification:

Recommended torque:	0,6 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 13: 36-000220

Contact assignment:

1) white	5) grey
2) brown	6) pink
3) green	7) blue
4) yellow	8) red

Part no:	Description:	Length L:	Cable:
43-10072	SAL - 12 - RK8 - 2 / A1	2m	PVC, grey, 8x0,25mm ² Cable: 781-A12800
43-10073	SAL - 12 - RK8 - 3 / A1	3m	
43-10074	SAL - 12 - RK8 - 5 / A1	5m	
43-10075	SAL - 12 - RK8 - 10 / A1	10m	
43-xxxxx	SAL - 12 - RK8 - ... / A1	x	

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: a 06.01.2011 VF Ä3767 Coupling nut modified, spanner flats added, data sheet modified	 dim. in mm	title: Female connector M12x1 axial	
	tolerance of cable: L ≤ 4m: L + 40mm L > 4m: L + 1%			
	general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm		dwg no: 43K1A091	
	THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH		part no: see table	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[43-10074](#) [43-10075](#) [43-10072](#) [43-10073](#)