


REV.	DATE	ECR NO.	DESCRIPTION
NC	01/16/09	—	INITIAL RELEASE



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex								
8						DRAWN	G.R.S.	01/16/09										
7						CHECKED												
6						ISSUED				PART DESCRIPTION								
5						SHEET	1 OF 1											
4						PART NO.					BNC P.C. MOUNT RECEPTACLE JACK							
3	CONTACT PIN	BER. COPPER	GOLD	1														
2	INSULATOR	PTFE	NATURAL	1		112586-13												
1	BODY	BRASS	NICKEL	1														
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE		C:/112/112586-13.DWG		DWG. NO.		112586-13.DWG		REV.	NC	SIZE	A	SCALE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112586-13](#)