





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
D	LEN1390206	2013/09/02	Lu Di	Update Dimension
E	LEN1460151	2014/06/24	Vicky	Update Dimension
F	C200380	2020/03/30	JC Chen	FXI



Panel Thickness
面板厚度
X(MAX.)

Screw L=5.0 For Panel Thickness
Under 1.2mm
適用板厚 1.2mm 以下

Screw L=6.0 For Panel Thickness
Between 1.2~2.0mm
適用板厚 1.2~2.0mm 以下





26Pin Female Connector
PCB Pin Layout

剖面線區域限高0mm

Note:

- * $\varnothing$ Important Dimension.
- * Waterproof Rate: IP68
IP68: 1M of depth of water 24 hours
- * Do Mating Test After Glued
- * HD-SUB Conn.: PBT, Black Core
- * Plastic Jacket: Nylon+GF, Black
- * Female Pin: Copper Alloy, Gold Plated
- * Ring: Silicone, Light Blue
- * Screw: Copper Alloy, Nickel Plated, #4-40 UNC



Recommended Panel Cut-Out
建議挖孔尺寸

UNIT: mm			TITLE	HD26/F Conn., Panel, PCB 90° Add Board Lock
TOLERANCE	.X ±0.25	.XX ±0.1	SCALE	1:1
.XXX ±0.05			SIZE	A4
ANGLES ±1°			SHEET	1 OF 1
			REV.	F
			WC-REV.	A.4
			QC	Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	HDB-26PFFP-SB8001	DRAWN BY	Vicky	DATE	2014-06-24
DWG NO	HDB-26PFFP-SB8001	CHECKED BY	Sam	DATE	2014-06-24
CUSTOMER	ALTW	APPROVED BY	Rita	DATE	2014-06-24

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HDB-26PFFP-SB8001](#)