

1		2		3		4		5		6		7		8	
				REV.	ECN NO.	DATE	SIGN	DESCRIPTION							
				C	LEN15A0226~29	2015/04/12	Jason.Yu	Update LOGO & Title							
				D	C190397	2019/04/03	Siou	Change SR Appearance.							
				E	C230772	2023/06/09	Alex	⚠*2							
				HDB-62AMMM-SL7AXX XX : 01~99Meters 01 : 01Meters 02 : 02Meters ... 99 : 99Meters Cable Length(L): 01~99Meters Note: * Ⓞ Important Dimension To Check. * Waterproof Rate: IP67 * Housing: ABS, Black * Conn.: D-Sub 62 Pin, Male * Gasket: EPDM, Black * Screw: Big EPC ⚠ * Cable: UL2464 (3IC*26#+MY)+3IC*26#+AL/MY+D, PVC Jacket(UV Resistant), OD=13.0, Black * Cable Length Tolerance: 1M~10M±5%mm, 11M~99M±500mm.											
UNIT:mm				TITLE ⚠ HD SUB 62P M CONN CABLE SCREW HD62P M CONN M PIN				ITEM NO				DRAWN BY Siou		DATE 2019/04/03	
TOLERANCE		±0.5 mm		SCALE 7:10		SIZE A4		SHEET 1 OF 2		DWG NO HDB-62AMMM-SL7AXX		CHECKED BY Eagle		DATE 2019/04/03	
REV. E		WC-REV. A.1		Ⓞ: Inspection item		Amphenol LTW 安費諾亮泰企業股份有限公司				CUSTOMER ALTW		APPROVED BY Neo		DATE 2019/04/03	
1		2		3		4		5		6		7		8	

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

1			2			3			4			5			6			7			8		
F						Shell	Drain					地線											
	31	Light Blue/Red		亮藍/紅	62	Light Blue/Red		亮藍/紅															
	30	Light Blue/Black		亮藍/黑	61	Light Blue/Black		亮藍/黑															
	29	Light Blue		亮藍	60	Light Blue		亮藍															
	28	Pink/Green		粉紅/綠	59	Pink/Green		粉紅/綠															
E	27	Pink/Blue		粉紅/藍	58	Pink/Blue		粉紅/藍															
	26	Pink/Red		粉紅/紅	57	Pink/Red		粉紅/紅															
	25	Pink/Black		粉紅/黑	56	Pink/Black		粉紅/黑															
	24	Gray/Black		灰/黑	55	Gray/Black		灰/黑															
	23	Green/Black		綠/黑	54	Green/Black		綠/黑															
D	22	Yellow/Black		黃/黑	53	Yellow/Black		黃/黑															
	21	Orange/Black		橘/黑	52	Orange/Black		橘/黑															
	20	Red/Black		紅/黑	51	Red/Black		紅/黑															
	19	Purple/White		紫/白	50	Purple/White		紫/白															
	18	Blue/White		藍/白	49	Blue/White		藍/白															
C	17	Green/White		綠/白	48	Green/White		綠/白															
	16	Orange/White		橘/白	47	Orange/White		橘/白															
	15	Red/White		紅/白	46	Red/White		紅/白															
	14	Brown/White		棕/白	45	Brown/White		棕/白															
	13	Black/White		黑/白	44	Black/White		黑/白															
B	12	Light Green		亮綠	43	Light Green		亮綠															
	11	Pink		粉紅	42	Pink		粉紅															
	10	White		白	41	White		白															
	9	Gray		灰	40	Gray		灰															
	8	Purple		紫	39	Purple		紫															
A	7	Blue		藍	38	Blue		藍															
	6	Green		綠	37	Green		綠															
	5	Yellow		黃	36	Yellow		黃															
	4	Orange		橘	35	Orange		橘															
	3	Red		紅	34	Red		紅															
		2	Brown		棕	33	Brown		棕														
		1	Black		黑	32	Black		黑														
Conn.		Wire Color			Conn.		Wire Color																
Group1 Pin Out					Group2 Pin Out																		
UNIT:mm				TITLE		HD SUB 62P M CONN		CABLE SCREW HD62P M CONN M PIN															
TOLERANCE		±0.5 mm		SCALE		7:10		SIZE		A4		SHEET		2 OF 2									
				REV.		E		MC-REV.		A.1		QC: Inspection item											

ALTW

CONFIDENTIAL

2015-10-13

R&D DEPT.

ITEM NO		DRAWN BY		DATE	
		Siou		2019/04/03	
DWG NO		CHECKED BY		DATE	
HDB-62AMMM-SL7AXX		Eagle		2019/04/03	
CUSTOMER		APPROVED BY		DATE	
ALTW		Neo		2019/04/03	

Amphenol LTW

安費諾亮泰企業股份有限公司

W10814-03-0001A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HDB-62AMMM-SL7A02](#) [HDB-62AMMM-SL7A01](#) [HDB-62AMMM-SL7A05](#) [HDB-62AMMM-SL7A10](#) [HDB-62AMMM-SL7A04](#) [HDB-62AMMM-SL7A03](#)