


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	C210637	2021/05/05	Vicky	 X1
D	C221201	2022/08/04	Lynne	 X3
E	C221882	2022/12/16	Vicky	 X1



- △C Note:
- * RoHS Compliant
 - * ○○○ Important dimension
- △E
- * Waterproof rate: IP67, mated
 - * Connector
- Housing: Thermoplastic, Black
- Pin: Copper alloy, Gold plated
- O-Ring: Rubber, Gray
- △B
- Nut: Metal
- Shield: Metal
- Outer mold: Thermoplastic, Black
- * Cable: UL2517, PVC Jacket, Black
 - * Cable length tolerance: 1M: +50/-0 mm

1M < L ≤ 3M:	+100 / -0	mm
3M < L ≤ 5M:	+150 / -0	mm
5M < L ≤ 10M:	±100	mm
10M < L ≤ 20M:	±200	mm
20M < L ≤ 30M:	±300	mm
30M < L ≤ 99M:	±500	mm

UNIT:mm				TITLE N SEN, M8W/KEY-SHLD, SCREW CABLE W/O SR, F, F, MOLDING			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY		DATE				
TOLERANCE		±0.5mm							SCALE 2:1		SIZE A4		SHEET 1 OF 2		DWG NO		CHECKED BY
REV. E				WC-REV. A.5		QC: Inspection item			M8AS-XXBFFM-SL7DXX		Rita		2020-04-29				
									CUSTOMER		ALTW		APPROVED BY		Max		2020-04-29

	1	2	3	4	5	6	7	8		
F							6P	5.8	24	M8AS-06BFFM-SL7DXX
							4P	5.0		M8AS-04BFFM-SL7DXX
							3P	4.6		M8AS-03BFFM-SL7DXX
E							Contacts	Cable OD	AWG	Item No.
D										
C										
B										
A										

</

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[M8AS-03BFFM-SL7D01](#) [M8AS-04BFFM-SL7D01](#) [M8AS-06BFFM-SL7D03](#) [M8AS-06BFFM-SL7D06](#) [M8AS-06BFFM-SL7D04](#) [M8AS-06BFFM-SL7D01](#) [M8AS-06BFFM-SL7D02](#) [M8AS-06BFFM-SL7D10](#) [M8AS-06BFFM-SL7D05](#) [M8AS-03BFFM-SL7D05](#) [M8AS-03BFFM-SL7D04](#) [M8AS-04BFFM-SL7D02](#) [M8AS-04BFFM-SL7D10](#) [M8AS-03BFFM-SL7D02](#) [M8AS-04BFFM-SL7D05](#) [M8AS-03BFFM-SL7D10](#) [M8AS-03BFFM-SL7D03](#) [M8AS-04BFFM-SL7D03](#) [M8AS-04BFFM-SL7D04](#) [M8AS-04BFFM-SL7D06](#)