

PRODUCT NUMBER
73304-XXXLF

PLATING OPTION
1= GXT 0.76 μ m
3= GOLD 0.76 μ m
5= GOLD 1.27 μ m


PACKAGE OPTION
1= TAPE ON REEL
2= TUBE
3= TAPE ON REEL
IN PLASTIC BAG

TERMINAL LOADING
1= FULLY LOADED
2= POS 1,2,7,8
3= POS 3,4,5,6



WHEN NEEDED, SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 4.

NOTES:

- 1- MATERIAL: HOUSING: HIGH TEMP. PCT, COLOUR BLACK.
TERMINAL: PHOSPHOR BRONZE.
- 2 - PLATING: CONTACT AREA: SEE TABLE.
SOLDER TAIL : 90/10 SnPb 2 μ m MIN.
WHEN SUFFIX "LF" IS REQUIRED, 2 μ m MIN MATTE
TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.
NO RAW EDGES EXEPT SOLDER TAIL TIPS
- 3 - SOLDER TAILS COPLANARITY : 0.1 mm
- 4 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE,
2 μ m MINIMUM MATTE TIN OVER 1.27 μ m
MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO
245°C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004
- 5 - PACKAGING FOR OPTION 3 : EACH REEL IS WRAPPED INTO A PLASTIC BAG
TO PROTECT FROM MOISTURE DURING STACKING TIME.




CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface ISO 1302		tolerance ISO 406 ISO 1101		projection 		product family MOD JACK			
ltr		ecn no		dr		date		tolerances unless otherwise specified		title			
H		F06-0240		DLE		06.07.18		angles		SMT RA JACK			
J		F09-0070		LSA		02.07.23		linear		8 POS OUTSIDE			
K		B-15798		JFA		13.09.09		±2'		mm 			
L		F-21888		AMA		15.09.09		engr		scale 2:1			
								D LEGRAND		dwg no			
								F TISSERAND		sheet 1 of 3			
F		F04-0363		DLE		04.10.18		chr		73304			
G		F05-0247		DLE		05.09.12		appd		A3			
								F.TI		type			
										CUSTOMER Drawing			
sheet		revision		L		E		B					
index		sheet		1		2		3					



FCconnect.com

Copyright FCJ



CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface ISO 1302 <input checked="" type="checkbox"/> ISO 406 ISO 1101		tolerance ISO 406 ISO 1101		projection 		product family MOD JACK	
ltr				ecn no		dr		date		title	
A				F04-0363		DLE		04.10.18		SMT RA JACK	
B				F06-0240		DLE		06.07.18		8 POS OUTSIDE	
angles				linear		±0.13		mm		scale 2:1	
±2°											
dr				D LEGRAND		04.10.18		FCJ		dwg no	
enrg				P NIZZI		04.10.18				sheet 3 of - size	
chr				D LEGRAND		04.10.18				73304 A4	
appd				P.NZ		04.10.18				type	
CUSTOMER Drawing											
sheet index				revision sheet							

form: A4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[73304-121LF](#)