


REV.	ECN NO.	DATE	SIGN.	DESCRIPTION
B	LEN-770205	2007/07/11	J. Espiritu	Revise Projection Of Polarization Key And Apply New Format
C	LEN15C0487~490	2015/12/21	Vicky	Update Logo & Note


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF AMPHENOL LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY AMPHENOL LTW.




Cable ②

BD-06BFFM-SL7000 ①
Color:Black


Conn.



BD-06BFMM-SL7AXX
 ↑
 XX:01~99Meter
 01:01Meter
 02:02Meters
 ⋮
 99:99Meters
 Cable Length(L):01~99Meters



- Note:
- * @C Important Dimension To Check.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black
 - * Female Pin: Copper Alloy, Gold Plated
 - * Cable: UL2464 24AWG*6C+D+Al/My, PVC Jacket, UV Resistant, OD=5.8mm, Black
 - * Cable Length Tolerance: 01M:±40mm
 02M~05M:±60mm
 06M~10M:±100mm
 11M~30M:±200mm
 31M~99M:±500mm



Pin Assignments
Front View

6	White	白
5	Red	紅
4	Orange	橘
3	Yellow	黃
2	Green	綠
1	Blue	藍
Conn.	Wire Color	Pin Out

UNIT:mm	
TOLERANCE	±0.5 mm

TITLE	Standard	
	Cable Screw 6Pin F Conn F Pin	
SCALE	Free	SHEET 1 OF 1
REV. C	SIZE A4	@C :Inspection Item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	
DWG NO	BD-06BFFM-SL7AXX
CUSTOMER	ALTW

DRAWN BY	Vicky
CHECKED BY	Rita
APPROVED BY	Lisa

DATE	2015/12/21
DATE	2015/12/21
DATE	2015/12/21

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[1BD-06BFFM-SL7A01](#)