



REV.	ECN NO.	DATE	SIGN	DESCRIPTION




DD-18AFFM-QR8D XX

XX : 01~99Meters
 01 : 01Meter
 02 : 02Meters
 ...
 99 : 99Meters

Cable Length(L): 01~99Meters



- Note:
- * \varnothing Important Dimension To Check.
 - * Working Voltage Rating: AC 300 V
 - * Working Current Rating: Max. 05A
 - * Flame Class: UL94V-0
 - * Waterproof Rate: IP68(Mated)
In 1 meter water within 24 hours.
 - * Housing: Nylon+GF, Black
 - * Female Pin: Copper Alloy, Gold & Ni Plated
 - * Cable: UL21388 20AWG*18C+AL.Mylar, PVC Jacket UV Resistant, OD=10.0, Black.
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



9	Gray	灰	18	Blue/White	藍/白
8	Purple	紫	17	Green/White	綠/白
7	Blue	藍	16	Orange/White	橙/白
6	Green	綠	15	Red/White	紅/白
5	Yellow	黃	14	Brown/White	棕/白
4	Orange	橙	13	Black/White	黑/白
3	Red	紅	12	Light Green	淡綠
2	Brown	棕	11	Pink	粉紅
1	Black	黑	10	White	白
Conn.	Wire Color		Conn.	Wire Color	
Pin Out			Pin Out		

UNIT:mm
 TOLERANCE ±0.5

TITLE X-Lok D Size Cable Molding
18Pin F Connector F Pin(05A)
 SCALE 1:1 SIZE A4 SHEET 1 OF 1
 REV. A WC-REV. A.2 \varnothing : Inspection item

Amphenol LTW
 安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Wes Fan	2016-05-23
DWG NO	CHECKED BY	DATE
DD-18AFFM-QR8DXX	Spring Liu	2016-05-23
CUSTOMER	APPROVED BY	DATE
ALTW	Kevin Hu	2016-05-23

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF AMPHENOL LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY AMPHENOL LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[DD-18AFFM-QR8D01](#)