



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1440191	2014/05/10	Tom	Updated The Note



Pin Out		
Wire Color		Plug
Drain Wire	接地	Shield
Brown	棕	8
Brown/white	棕白	7
Green	綠	6
Blue/white	藍白	5
Blue	藍	4
Green/white	綠白	3
Orange	橙	2
Orange/white	橙白	1

RCP-5SAMMM-SLM7BXX

XX: 01~99Meter
 01: 01Meter
 02: 02Meters
 ...
 99: 99Meters
 Cable Length(L):01~99Meters

X:
 (B)CAT5E FTP

- Note:
- * ⊘ Important Dimension
 - * Waterproof Rate: IP67.
 - * Plug: PC, UL94V-2, Gold Plated, Shielded
 - * $\triangle B$ Screw Nut: Nylon+GF, Black.
 - * Gasket: EPDM, Black.
 - * Cable: 24AWG*4P, Black, UV Resistant
 (B)CAT5E FTP, OD Max.: $\text{⊘}6.5$.
 - * Cable Length Tolerance:
 - 01M: $\pm 40\text{mm}$
 - 02~05M: $\pm 60\text{mm}$
 - 06~10M: $\pm 100\text{mm}$
 - 11~30M: $\pm 200\text{mm}$
 - 30~99M: $\pm 500\text{mm}$

UNIT: mm		TITLE RJ45, C SIZE CABLE SCREW 5E M CONN M PIN			Amphenol LTW 安費諾亮泰企業股份有限公司	ITEM NO	DRAWN BY	DATE
		SCALE 1:1	SIZE A4	SHEET 1 OF 1		DWG NO RCP-5SAMMM-SLM7BXX	CHECKED BY Jerry	DATE 2014-05-10
TOLERANCE .X ± 0.25 .XX ± 0.1 .XXX ± 0.05 ANGLES $\pm 1^\circ$		REV. B	WC-REV. B.3	⊘ : Inspection item	CUSTOMER ALTW	APPROVED BY VICTOR	DATE 2014-05-10	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RCP-5SAMMM-SLM7B01](#)