




FCIconnect.com


Copyright FCI



PT. NO.	PARTS NAME	MATERIAL	Q'TY	NOTE
1	HOUSING	GLASS FILLED THERMOPLASTIC RATED (UL94V-0)	1	COLOR:BRACK
2	CONTACT	BRASS	n	PLATING CONTACT AREA:GOLD OVER NICKL TERMINAL AREA:TIN (LEAD FREE)
3	MOUNTING PLATE	PHOSPOR BRONZE	2	PLATING:TIN (LEAD FREE)

RECOMMENDED PC BOARD LAYOUT  
THICKNESS : 1.6  
HOLE PATTERN (COMPONENT SIDE)

n:NO. OF CONTACTS  
(10 TO 30 , ONLY EVEN POS.)



NOTE  
1.This product meets European Union Directives and other country regulations as described in GS-22-008.

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family 590F			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title FLOATING BOARD TO BOARD RECEPTACLE CONNECTOR (GOLD PLATING AND LEAD FREE) (Cat. No. BTFW_R-3RDA7MLF)			
A	J07-0021	M.K	Jan.25,07	angles	linear	±0.3				
				dr	K.Higuchi	Jan.25,07	dwg no sheet 1 of 1 size JSA 97219 A4			
				enrg	M.Koga	Jan.25,07				
				chr	K.Higuchi	Jan.25,07	type Product Customer Drawing			
				appd	M.Koga	Jan.25,07				
sheet index	revision sheet									Rev A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[BTFW10R-3RDA7MLF](#) [BTFW30R-3RDA7MLF](#) [BTFW18R-3RDA7MLF](#) [BTFW20R-3RDA7MLF](#) [BTFW22R-3RDA7MLF](#)