

1

2

3

4

A

A

B



B

C

C

D

D



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:  
SEE GS-12-447

- NOTE-1: COMPATIBLE WITH NARROW AND WIDE BODY  
NOTE-2: PCB FINISH HOLE DIAMETER GS-12-447  
NOTE-3: STANDARD PACKAGING IS IN TUBE ,BUT IF SUFFIX "P" IS ADDED IN P/N ,PACKAGING IS IN TRAYS ,BUT CONNECTOR MARKING IS WITHOUT "P"  
Example: HM1FxxxxxxxH6PLF, marking: HM1FxxxxxxxH6LF

- SPECIFIC DATAS:  
Visual inspection : 100%  
- Marking failures  
- Housing material failures  
- Spoilt housing  
- Stained housing  
- Broken contacts ( twisted or loosen )

△ PART NUMBER  
HM1S51FER400H\*(LF)

LF = FOR LEAD FREE PRODUCT  
PLATING CODE:  
6 = TELCORDIA CO  
E = CUSTOMER SPECIAL, CONTACT  
30u" GOLD SELECTIVE PLATING.

rev	ecn no	dr	date
A	-	-	2001/01/26
B	LS05-004	MLE	2005/02/22
C	LS06-0095	LGO	2006/07/05
D	LS06-0159	MLE	2006/10/24
E	LS07-0266	MLE	2007/11/09
F	DG09-0367	TER	2009-11-25
-	-	-	-

www.fciconnect.com		surface ISO 1302 ✓	tolerance std ISO 406 ISO 1101	projection	mm
		TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	PERRICHOT	2001/01/26	ANGULAR	0.X	±0.1
Eng	LENOIR	2001/01/26	LINEAR	0.XX	±0.1
Chr	LEGARE	2001/01/26	0.XX ±2	0.XXX	±0.1
Appr	LEGARE	2001/01/26	Product family		METRAL
				size	A3
				ECN	DG09-0367
				Spec ref	-
title			METRAL FEM. 5 ROW STRAIGHT PRESS FIT		Rev.
catalog no			PCB THICKNESS: 2.4 mm MINIMUM		F
			dwg no		C-8626-11113
			CUSTOMER		sheet 1 of 1

European Views

1

2

3

4



Copyright FCI.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[HM1S51FER400HEPLF](#)