



Heyco® Stainless Steel Cable Ties


Ball Lock Stainless Steel Strip Cable Ties - Standard and PVC Coated

PART SPECIFICATIONS				PART NO.		DESCRIPTION	PART DIMENSIONS			
Min. Tensile Strength		Max. Bundle Diameter		Standard Steel	PVC Coated Black		A Length		B Width	
Lbs.	N	in.	mm.			in.	mm.	in.	mm.	
AISI 304										
112	500	1.18	30,0	12801	12801B	NTSS-0150-46A	5.91	150,0	.18	4,6
		2.05	52,0	12802	12802B	NTSS-0200-46A	7.87	200,0		
		2.68	68,0	12803	12803B	NTSS-0250-46A	9.84	250,0		
		3.23	82,0	12805	12805B	NTSS-0300-46A	11.81	300,0		
		3.86	98,0	12806	12806B	NTSS-0350-46A	13.78	350,0		
		4.33	110,0	12808	12808B	NTSS-0400-46A	15.75	400,0		
		5.75	146,0	12810	12810B	NTSS-0500-46A	19.69	500,0		
		7.09	180,0	12812	12812B	NTSS-0600-46A	23.62	600,0		
		9.50	240,0	12814	12814B	NTSS-0800-46A	31.50	800,0		
250	1115	2.05	52,0	12821	12821B	NTSS-0200-79A	7.87	200,0	.31	7,9
		2.68	68,0	12822	12822B	NTSS-0250-79A	9.84	250,0		
		3.23	82,0	12824	12824B	NTSS-0300-79A	11.81	300,0		
		3.86	98,0	12825	12825B	NTSS-0350-79A	13.78	350,0		
		4.33	110,0	12827	12827B	NTSS-0400-79A	15.75	400,0		
		5.75	146,0	12829	12829B	NTSS-0500-79A	19.69	500,0		
		7.09	180,0	12831	12831B	NTSS-0600-79A	23.62	600,0		
		8.27	210,0	12833	12833B	NTSS-0700-79A	27.56	700,0		
		9.50	240,0	12834	12834B	NTSS-0800-79A	31.50	800,0		
		12.09	307,0	12836	12836B	NTSS-1000-79A	39.37	1000,0		
		AISI 316								
112	500	1.18	30,0	12851	12851B	NTSS-0150-46B	5.91	150,0	.18	4,6
		2.05	52,0	12852	12852B	NTSS-0200-46B	7.87	200,0		
		2.68	68,0	12853	12853B	NTSS-0250-46B	9.84	250,0		
		3.23	82,0	12855	12855B	NTSS-0300-46B	11.81	300,0		
		3.86	98,0	12856	12856B	NTSS-0350-46B	13.78	350,0		
		4.33	110,0	12858	12858B	NTSS-0400-46B	15.75	400,0		
		5.75	146,0	12860	12860B	NTSS-0500-46B	19.69	500,0		
		7.09	180,0	12862	12862B	NTSS-0600-46B	23.62	600,0		
		9.50	240,0	12864	12864B	NTSS-0800-46B	31.50	800,0		
250	1115	2.05	52,0	12871	12871B	NTSS-0200-79B	7.87	200,0	.31	7,9
		2.68	68,0	12872	12872B	NTSS-0250-79B	9.84	250,0		
		3.23	82,0	12874	12874B	NTSS-0300-79B	11.81	300,0		
		3.86	98,0	12875	12875B	NTSS-0350-79B	13.78	350,0		
		4.33	110,0	12877	12877B	NTSS-0400-79B	15.75	400,0		
		5.75	146,0	12879	12879B	NTSS-0500-79B	19.69	500,0		
		7.09	180,0	12881	12881B	NTSS-0600-79B	23.62	600,0		
		8.27	210,0	12883	12883B	NTSS-0700-79B	27.56	700,0		
		9.50	240,0	12884	12884B	NTSS-0800-79B	31.50	800,0		
		12.09	307,0	12886	12886B	NTSS-1000-79B	39.37	1000,0		

NEW PRODUCT



- For ease of assembly, position locking head so that the widest end is down.
- Part Description Key: NTSS-XXXX-YYA where XXXX = length (mm) and YYA = width (mm) with A indicating AISI 304 stainless steel and B indicating AISI 316 stainless steel.
- Stainless steel cable ties have more strength and better durability than nylon cable ties.
- Locking ball design for maximum holding strength and ease of installation.
- Coated ties offer additional protection and separation of dissimilar metals for improved corrosion resistance.
- Suitable for harsh outdoor environments; conform to standard IEC92 for Marine Electrical Appliances and the requirements of CB1113-85 “Plastic Covered Metal Cable Ties”, “Steel Sea Boats Construction Level Standard.”
- Secure bundles in moist and high temperature environments with decay, fire, corrosion, and radio resistance.
- Widely used in shipping, communication, and flight applications.
- .010" (0,25 mm) thick.
- Custom lengths available.
- 100 pack standard.



Materials AISI 304 or 316 stainless steel with PVC coating

Quick Specs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[12856](#)