

"Stay Connected" with



Solar Power Components

a PennEngineering® Company




- **Releasable and reusable** ties for easy bundling, closing, bagging, holding, and tying.
- Polyethylene for high flexibility and moderate strength.
- Multiple sizes for bundles up to 4" (101,6 mm) diameter.

Heyco® Beaded Ties

TENSILE STRENGTH		MAXIMUM BUNDLE DIAMETER		DESC.	PART NUMBERS						
					NYLON		POLYETHYLENE				
Lbs.	N	in.	mm.		Black	Natural	Black	Natural	Blue	Red	Yellow
Standard											
10	45	1-1/8	28,6	BT 4	3509	3490	3419	3420	3421	3422	3423
		1-3/8	35,0	BT 5	3519	3491	3424	3425	3426	3427	3428
		1-7/8	48,0	BT 6	3523	3492	3429	3430	3431	3432	3433
		2-1/2	64,0	BT 8	3524	3493	3434	3435	3436	3437	3438
		3	76,0	BT 10	3495	3494	3439	3440	3441	3442	3443
		4	101,6	BT 14	3498	3496	3484	3480	3476	3482	3483



Standard colors: PE-black, natural, blue, red, and yellow. N-Black and natural.

*Mounts into a .250" (6,4 mm) diameter hole, maximum panel thickness .142" (3,6 mm).



Mounting Platform for Beaded Ties

- Part No. **3750**
- Adhesive backed
- May also be screw mounted
- Molded of natural nylon.



Quick Specs

Material	Polyethylene or Nylon
Flammability Rating	94V-2
Temperature Range	40°F (0°C) to 221°F (85°C)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3499](#)