

MICRO SWITCH

FREEPORT ILLINOIS, U S A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING
BE-2RQ1-A2

BE-2RQ1-A2

M

DRAWING
NUMBER

8

5

ISSUE

8

REPLACES X69099-BE

RELEASE NO. PR-7948

CHECK

REVISIONS

A	CO	58782	WJM	25 JAN 86
B	CO-	73267-J	JAL	22 NOV 93
C	CO	77590	SAD	9 JUN 94
D	CO-82133		CSL	26 JUL 96

CHECK

19 JUNE 79

19 JUNE 79

19 JUNE 79


19 JUNE 79

19 JUNE 79

19 JUNE 79

19 JUNE 79


19 JUNE 79



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- 2 HARDWARE FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CHARACTERISTICS

OPERATING FORCE ----- 14-22 OZ
RELEASE FORCE ----- 10 OZ MIN
DIFFERENTIAL TRAVEL ----- .0020 - .0075
OVERTRAVEL ----- .094 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

25A-125 or 250VAC
1HP-125VAC; 2HP-250VAC
PILOT DUTY 750VA-125, 250, 277VAC
60/75°C (C_u)



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE:

	DIM.	TOL.	DIM.	TOL.
	mm	mm/in	in	mm/in
NO PLACES	X	1/.04	X	0.07/03
ONE PLACE	X.X	0.4/018	X.X	0.38/015
TWO PLACES	X.XX	0.18/008	X.XX	0.13/005
THREE PLACES	X.XXX		X.XXX	
ANGLES				

DESIGN UNITS ☐ SI METRIC ☐ US CUSTOMARY

WEIGHT .084 LB

FORMTEK

FO-52848-A

DRAWN

J A P 13 JUN 79

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BE-2RQ1-A2](#)